





**4-CHANNEL DIGITAL OUTPUT  
MODULE DC 24 V 0,5 A  
750-504**

<b>ITEM-NO. (ITEM-NO.)</b>	750-504
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.08 - 2.5
<b>Cross section2 (Cross section / AWG)</b>	28 - 14
<b>Strip length (Strip length / mm)</b>	8 - 9
<b>Height (Height / mm)</b>	64
<b>Width (Width / mm)</b>	12
<b>Depth (Depth / mm)</b>	100
<b>COLOR (COLOR)</b>	lichtgrau
<b>WEIGHT (WEIGHT / g)</b>	49.5
<b>Comment (Comment)</b>	24V DC 0,5 A