



Data

Connection data

Solid conductor	0.08 ... 2.5 mm ² / 28 ... 14 AWG
Strip length	9 ... 10 mm / 0.35 ... 0.39 Inch

Geometrical Data

Width	12 mm / 0.472 inch
Depth	74.3 mm / 2.925 inch

Mechanical data

Pluggable connector	yes
---------------------	-----

Material Data

Color	gelb
Fire load	0.201 MJ
Weight	11.23 g

Environmental Requirements

Surrounding air (operating) temperature	0 ... 55 °C
Surrounding air (storage) temperature	-25 ... 85 °C
Degree of protection	IP20



Commercial data

Country of origin	CN
GTIN	4045454372064
Customs Tariff No.	85366990990
Product Group	15 (Remote I/O)

Downloads

Documentation

Bid Text

753-120	Jan 22, 2016	DOC 22.5 kB	Download
---------	--------------	----------------	----------

Product family

750/753 Series I/O-System

[Learn more about the product family.](#)

[Show all products from the family](#)

Subject to changes.