



RoHS
Compliant

BOMcheck.net

Color: ■

Data

Connection data

Solid conductor	0.08 ... 2.5 mm ² / 28 ... 14 AWG
Strip length	9 ... 10 mm / 0.35 ... 0.39 Inch

Geometrical Data

Width	12 mm / 0.472 inch
Height from upper-edge of DIN-35 rail	64 mm / 2.52 inch
Depth	100 mm / 3.937 inch

Mechanical data

Pluggable connector	yes
---------------------	-----

Material Data

Color	red
Fire load	0.002 MJ
Weight	0.1 g



Environmental Requirements

Surrounding air (operating) temperature	0 ... 55 °C
Surrounding air (storage) temperature	-25 ... 85 °C

Commercial data

Country of origin	DE
GTIN	4044918924856
Customs Tariff No.	39269097900
Product Group	15 (Remote I/O)

Downloads

Documentation

Bid Text

753-150 IO, Zubehoer	Jan 22, 2016	DOC 22.0 kB	Download
-------------------------	--------------	----------------	----------

Product family

750/753 Series I/O-System

[Learn more about the product family.](#)

[Show all products from the family](#)

Subject to changes.