





**2-Channel digital input module DC 24 V proximity switch positive switching  
2- to 4-conductor-connection  
753-410**

<b>ITEM-NO. (ITEM-NO.)</b>	753-410
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.08 - 2.5
<b>Cross section2 (Cross section / AWG)</b>	28 - 14
<b>Strip length (Strip length / mm)</b>	9 - 10
<b>Height (Height / mm)</b>	64
<b>Width (Width / mm)</b>	12
<b>Depth (Depth / mm)</b>	100
<b>COLOR (COLOR)</b>	lichtgrau
<b>Comment (Comment)</b>	24 V DC 3.0 ms, Nahrungsinitiator