



RoHS
Compliant

BOMcheck.net

Item description

Notes on operating the antenna with WAGO EnOcean radio receivers:

- The antenna is to be mounted on a plate measuring at least 9.8 x 9.8 inches (25 x 25 cm).
- The distance of interfering sources to the antenna and antenna line must be at least 11.8 inches (30 cm) and the free space between the antenna and the next wall must be at least 13.78 inches (35 cm).
- The antenna cable should, under no circumstances, be bent sharply, since irreversible damage may result to the antenna line (RG174 bend radius > 0.6 inches/15 mm).

Data

Technical Data

Wireless technology	Mobile communications
Frequency band	870 MHz ... 960 MHz; 1710 MHz ... 1880 MHz
Gain	870 MHz ... 960 MHz 0 dB; 1710 MHz ... 1880 MHz 0 dB
Max. Power	20 W
VSWR	870 MHz ... 960 MHz < 1.5; 1710 MHz ... 1880 MHz < 1.5

Mechanical data

Connector	SMA right angle plug + ferrite bead
-----------	-------------------------------------



Length of the connecting cable	2.5 m
--------------------------------	-------

Material Data

Weight	79.2 g
--------	--------

Commercial data

Country of origin	IT
GTIN	4044918122535
Customs Tariff No.	85177000000
Product Group	27 (Special components I/O)

Downloads**Documentation****Bid Text**

758-910 Zubehör 758	Nov 3, 2017	DOC 26.1 kB	Download
------------------------	-------------	----------------	----------

Additional Information

Disposal; Electrical and electronic equipment, Packaging	Oct 15, 2018	265.8 kB	Download
--	--------------	----------	----------

System Description

Radio Technology – General Product Information	Jun 6, 2017	925.9 kB	Download
--	-------------	----------	----------

Subject to changes.