



RoHS 
Compliant

[BOMcheck.net](https://www.bomcheck.net)

Item description

PTM 250 ist ein universell einsetzbarer, äußerst flacher Funkschalteneinsatz mit wartungsfreiem Energiegenerator.

Der Universal-Schalteneinsatz passt in zahlreiche Rahmenprogramme verschiedener Installationsmaterialhersteller. Die Bodenplatte ist kleb- oder schraubbar und damit sowohl auf Glas als auch auf Putz einfach anzubringen. Die Integration in den Rahmen erfolgt dabei ähnlich, wie bei Universaleinsätzen für Antennensteckdosen.

Lieferung erfolgt ohne Rahmen, diese müssen entsprechend gewünschtem Herstellerprogramm separat bestellt werden!

Note:

Weitere technische Daten sind den als Download zugeordneten Datenblättern zu entnehmen.

Data

Technical Data

Wireless technology	EnOcean 868 MHz, RPS type 2
Transmission range	300 m in open air, 30 m (typ.) within buildings
Antenna	Integrated EnOcean PTM 200 Radio Transmitter

**Geometrical Data**

Width	71 mm / 2.795 inch
Height	14 mm / 0.551 inch
Depth	71 mm / 2.795 inch

Material Data

Color	pure white
Weight	51.8 g

Environmental Requirements

Surrounding air (operating) temperature	-25 ... 65 °C
Relative air humidity (no condensation)	95 %

Commercial data

Country of origin	DE
GTIN	4045454271633
Customs Tariff No.	85365080990

Downloads**Documentation****Bid Text**

758-940/001-000 EnOcean	Jan 21, 2016	DOC 27.6 kB	Download
----------------------------	--------------	----------------	----------

Additional Information

Disposal; Electrical and electronic equipment, Packaging	Oct 15, 2018	265.8 kB	Download
--	--------------	----------	----------

System Description

Radio Technology – General Product Information	Jun 6, 2017	925.9 kB	Download
--	-------------	----------	----------

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.