

**SKMU MS EMV (brass locknut - EMC)
SKMU EMV M20****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Weidmüller has a variety of different cable and wire entry systems in the Portfolio: with different designs of plastic, brass and stainless steel cable glands in the IP66, 67, 68 or IP69k protection classes. As a complete alternative to cable glands, pre-assembled cables with modular multi-wire or multi-cable entry systems can be simply and quickly inserted into electrical equipment. Last but not least, Weidmüller offers EX-certified cable glands and cable/wire entry systems.

- Cable glands made from plastic and brass
- EMC screwed joints
- for areas at risk of explosion
- VDE, CSA and UL approvals

General ordering data

Type	SKMU EMV M20
Order No.	1777630000
Version	SKMU MS EMV (brass locknut - EMC), Locknut, M 20, 3.6 mm, Brass, nickel-plated
GTIN (EAN)	4032248157907
Qty.	100 pc(s).

SKMU MS EMV (brass locknut - EMC) SKMU EMV M20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	5.8 g
------------	-------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Width

Thickness	1 mm
-----------	------

General information

AF size 1	24 mm	Cable glands	metric
External thread	M 20	Internal thread	M 20
Length of thread	3.6 mm	Material	Brass, nickel-plated
O.D.	26.56 mm	Pitch of thread	1.5 mm
Thickness	1 mm		

Classifications

ETIM 3.0	EC000940	ETIM 4.0	EC000441
ETIM 5.0	EC000441	ETIM 6.0	EC000940
UNSPSC	30-21-18-01	eClass 5.1	23-11-07-01
eClass 6.2	27-14-91-09	eClass 7.1	27-14-91-09
eClass 8.1	27-14-91-09	eClass 9.0	27-14-44-24
eClass 9.1	27-14-44-24		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN.WSCAD
Engineering Data	STEP

SKMU MS EMV (brass locknut - EMC) SKMU EMV M20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

