

Inline plug - IB IL SCN-8-GY - 2862783

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Connector, unprinted, gray

Key commercial data

package_quantity	10
GTIN	4017918896416

Technical data

Dimensions

Height	111.2 mm
Depth	41 mm
Width	12 mm

classifications

eCl@ss

eCl@ss 4.0	27250281
eCl@ss 4.1	27250281
eCl@ss 5.0	27259205
eCl@ss 5.1	27242692
eCl@ss 6.0	27242692
eCl@ss 7.0	27242692
eCl@ss 8.0	27242692

ETIM

ETIM 2.0	EC000313
ETIM 3.0	EC000313
ETIM 4.0	EC002584
ETIM 5.0	EC002584

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	39121311
UNSPSC 12.01	39121311

Inline plug - IB IL SCN-8-GY - 2862783

classifications

UNSPSC

UNSPSC 13.2	39121311
--------------------	----------

approvals

UL Recognized / cUL Recognized / cULus Recognized /

Approval details

UL Recognized	
Nominal voltage UN	24 V
Nominal current IN	10 A
mm ² /AWG/kcmil	26-16

cUL Recognized	
Nominal voltage UN	24 V
Nominal current IN	10 A
mm ² /AWG/kcmil	26-16

cULus Recognized	
-------------------------	--

Drawings