

**Accessories
GWDR M20-PO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The range of cable glands is rounded off by a large number of accessories.

General ordering data

Type	GWDR M20-PO
Order No.	1777940000
Version	Sealing ring, Polyethylene, External thread: M 20
GTIN (EAN)	4032248158201
Qty.	100 pc(s).

Accessories GWDR M20-PO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	0.2 g
------------	-------

Width

Thickness	2 mm
-----------	------

General information

Cable gland	metric	Diameter of sealing ring	25 mm
External thread	M 20	Inside diameter D2	20.4 mm
Material	Polyethylene	O.D.	24 mm
Operating temperature range, max.	90 °C	Operating temperature range, min.	-30 °C
Pitch of thread	1.5 mm	Sealing	PE-HD
Thickness	2 mm		

Classifications

ETIM 3.0	EC000781	UNSPSC	31-16-18-18
eClass 5.1	23-07-90-90	eClass 6.2	27-14-91-09
eClass 7.1	27-14-91-09		

Product information

Descriptive text ordering data	Further versions on request
--------------------------------	-----------------------------

Approvals

Approvals	
ROHS	Conform

Accessories GWDR M20-PO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

