

Datenblatt

Technische Spezifikation für Sicherungshalter 325029

Material Housing	Polypropylene	
Material terminal	Brass	
	Component analyses	
	Cu:	55.40
	Pb:	0.0001
	Fe:	0.0100
	Sn:	0.000
Zn:	REM	
Electric control	Contact resistant when PVC cable is used:	
	0.75 mm ²	0.99 mOhm
	Contact resistant when PVC cable is used:	
	1.5 mm ²	1.06 mOhm
Character test	Tensile strength	40.0 Kgf/mm ²
	Extension	42.9%
	Harness	115 HV
Contact resistance Power after 1 hour 0.75 mm ²	10.0 Amp	1.03 mOhm
	15.0 Amp	1.10 mOhm
	20.0 Amp	1.18 mOhm
Contact resistance Power after 1 hour 1.5 mm ²	10.0 Amp	1.01 mOhm
	15.0 Amp	1.08 mOhm
	20.0 Amp	1.18 mOhm