

**Clamping yoke
KLBUE 3-8 SC**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Shielding and earthing

Our protective earth conductor and shielding terminals featuring different connection technologies allow you to effectively protect both people and equipment from interference, such as electrical or magnetic fields. A comprehensive range of accessories rounds off our range.

General ordering data

Type	KLBUE 3-8 SC
Order No.	1791220000
Version	Clamping yoke, Clamping yoke, Steel
GTIN (EAN)	4032248222 179
Qty.	100 pc(s).

**Clamping yoke
KLBUE 3-8 SC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmüller.com

Technical data**Dimensions and weights**

Width	14.5 mm	Width (inches)	0.571 inch
Height	18.5 mm	Height (inches)	0.728 inch
Depth	26 mm	Depth (inches)	1.024 inch
Mounting dimension - width	13.5 mm	Net weight	12.28 g

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C		

Material data

Material	Steel	Colour	silver
----------	-------	--------	--------

System specifications

Version	For a shield connection
---------	-------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of mounting	Screw		

Conductors for clamping (rated connection)

Cable diameter, max.	8 mm	Cable diameter, min.	3 mm
----------------------	------	----------------------	------

Classifications

ETIM 3.0	EC000489	ETIM 4.0	EC000489
ETIM 5.0	EC000489	ETIM 6.0	EC002020
eClass 6.2	27-14-11-90	eClass 7.1	27-14-11-50
eClass 8.1	27-14-11-50	eClass 9.0	27-14-11-50
eClass 9.1	27-14-11-50		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Engineering Data	STEP
User Documentation	Beipackzettel_KLBUE.pdf