

HDC enclosures HDC 06B ALU O-RING

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | |
|------------|---|
| Type | HDC 06B ALU O-RING |
| Order No. | 1019870000 |
| Version | HDC enclosures, Size: 3, Protection degree: IP65, Bulkhead enclosure, End-locking clamp, lower side, Standard |
| GTIN (EAN) | 4032248731985 |
| Qty. | 1 pc(s). |

**HDC enclosures
HDC 06B ALU O-RING**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|----------------------------|---------|-----------------------------|------------|
| Width | 66 mm | Width (inches) | 2.598 inch |
| Height | 27.8 mm | Height (inches) | 1.094 inch |
| Mounting dimension - width | 70 mm | Mounting dimension - height | 32 mm |
| Net weight | 102 g | | |

Temperatures

| | |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

Environmental Product Compliance

| | |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

Dimensions

| | | | |
|----------------------|--------|----------------------|---------|
| Height of base B1 | 5.3 mm | Height of housing B | 27.8 mm |
| Hole pitch length A2 | 70 mm | Total length housing | 60 mm |
| Width base C1 | 47 mm | Width housing C | 43 mm |

General data

| | | | |
|-----------------------------|-----------------------------|-----------------------|-------------------|
| EMC housings | No | Housing main material | diecast aluminium |
| Material of locking element | Stainless steel, rust-proof | Protection degree | IP65 |
| Surface finish | Powder coating | | |

Version

| | | | |
|------------------------|--------------------|--------------------------|-------------------------------|
| Clamp version | End-locking clamp | Design | Standard |
| Design of housing | Bulkhead enclosure | Design of locking system | End-locking clamp, lower side |
| Sealing | NBR | Size | 3 |
| Suitable for ModuPlug® | Yes | Top part/bottom part/lid | lower part |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000437 | ETIM 4.0 | EC000437 |
| ETIM 5.0 | EC000437 | ETIM 6.0 | EC000437 |
| UNSPSC | 30-21-18-01 | eClass 5.1 | 27-14-34-19 |
| eClass 6.2 | 27-26-12-03 | eClass 7.1 | 27-44-02-02 |
| eClass 8.1 | 27-44-02-02 | eClass 9.0 | 27-44-02-02 |
| eClass 9.1 | 27-44-02-02 | | |

Approvals

Approvals



ROHS

Conform

Data sheet**HDC enclosures
HDC 06B ALU O-RING**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Downloads**

| | |
|--------------------|---|
| Brochure/Catalogue | CAT 3 HDC 17/18 EN FL FIELDWIRING EN |
| Engineering Data | EPLAN, WSCAD |
| Engineering Data | STEP |

Data sheet

**HDC enclosures
HDC 06B ALU O-RING**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

