

**SAIL-VSA-M8W-3-3.0U****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



This valve plug has a transparent housing with an integral seal. The connection cross-section corresponds to 0.5 mm<sup>2</sup> and can therefore be connected directly to our SAI IDC distributor. The operating status of the valve plug is indicated by an LED. All the valve plugs have a protective circuit. The Weidmüller range of products comprises valve plugs type A, B and C to DIN and industry standards. In the plugged condition they achieve IP 67 class of protection.

**General ordering data**

Type	SAIL-VSA-M8W-3-3.0U
Order No.	<a href="#">1026190300</a>
Version	Valve plug, A
GTIN (EAN)	4032248753727
Qty.	1 pc(s).

## SAIL-VSA-M8W-3-3.0U

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Net weight	125 g
------------	-------

### Technical specifications for cable

No. of poles	3	Core cross-section	0.34 mm <sup>2</sup>
Sheath material	PUR	Sheathing colour	Black
Cable length	3 m		

### General technical data

Coding	Design A (18 mm), M8 = none	Protection degree	IP 67 (when screwed in)
Contact surface	tinned	LED	Yes
Rated voltage	24 V	Rated current	4 A
Temperature range of housing	-25...+80 °C		

### Classifications

eClass 6.2	27-06-91-90	eClass 7.1	27-06-91-90
------------	-------------	------------	-------------

### Approvals

Approvals	
ROHS	Conform