

FPL 4G2.5/P/F/3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Take advantage of our pre-assembled FieldPower® connectors with HQ connectors acc. to IEC 23570 (DESINA) for connecting decentralised motor controller devices quickly and conveniently.

General ordering data

Type	FPL 4G2.5/P/F/3
Order No.	1059190000
Version	FieldPower®, Cable, No. of wires: 4, Ölflex Classic 110 4G2.5 or similar, Cross-section: 2.5 mm ² , 3 m
GTIN (EAN)	4032248805891
Qty.	1 pc(s).

FPL 4G2.5/P/F/3

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 573 g

Temperatures

Operating temperature

Storage temperature

General data

Bending radius, min., moving	133.5 mm	Bending radius, min., stationary	35,6 mm
Cable length, string 1	3 m	Cross-section	2.5 mm ²
Halogen	Yes	Line type	Ölflex Classic 110 4G2.5 or similar
No. of wires	4	Temperature range, moving, max.	70 °C
Temperature range, moving, min.	-5 °C	Temperature range, stationary, max.	70 °C
Temperature range, stationary, min.	-40 °C	Wire assignments	see picture

Pre-assembly page 1

Connection 1 PTS4

Pre-assembly page 2

Connection 2 Wire-end ferrule

Technical data

Rated voltage 500 V

Classifications

eClass 6.2 27-06-91-90 eClass 7.1 27-06-91-90

Datenblatt

FPL 4G2.5/P/F/3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

