

**Device markers
THM GEW 15/6 GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



THM GEW woven-fabric labels are made from a very flexible cotton fabric. Delivery on reels for use with thermal transfer printers enables an adhesive layer which is thicker than that of A4 sheets for office laser printers. Together, this flexibility and the thick adhesive layer ensure higher adhesive strength and enable use on angular or round objects such as e.g. cables or hoses.

General ordering data

Type	THM GEW 15/6 GE
Order No.	1059790000
Version	Device markers, Label, 15 x 6 mm, Vinyl-coated cotton fabric, Colour: Yellow
GTIN (EAN)	4032248808182
Qty.	1 pc(s).

Device markers THM GEW 15/6 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	15 mm	Width	6 mm
Net weight	386 g		

General data

Adhesive	Natural rubber adhesive	Colour	Yellow
Material	Vinyl-coated cotton fabric	Material colour according to resistance code	4
Number per roll	10,000	Number per sheet	10,000
Operating temperature range, max.	80 °C	Operating temperature range, min.	-29 °C
Printing method	Thermotransfer	UL 94 flammability rating	HB
UL 969 flammability rating	No		

Classifications

ETIM 3.0	EC001288	UNSPSC	55-12-16-00
eClass 5.1	27-14-91-29	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

Approvals

Approvals	
ROHS	Conform

Downloads

M-Print® PRO configuration file	lab_thm_gew_15_6_mcf.zip
---------------------------------	--