

HDC enclosures
HDC IP68 16B SS 2M40**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The new RockStar® enclosures are resistant to seawater and offer a high degree of shock resistance, meet IP 68 and IP 69K, and have been developed for use under extreme environmental conditions and designed for the high vibration requirements acc. to DIN EN 61373 cat. 2 (bogie). As such, this housing family is ideally suited for fault- and maintenance-free operation of heavy-duty connectors in transport and traffic engineering as well as in power engineering and in applications with extreme requirements. During development, measures were also implemented to make the enclosures extremely EMC-resistant.

General ordering data

Type	HDC IP68 16B SS 2M40
Order No.	1081370000
Version	HDC enclosures, Size: 6, Protection degree: IP68, IP69K, Base enclosure, Screw plug, Standard, Size of cable entries: M 40
GTIN (EAN)	4032248877423
Qty.	1 pc(s).

HDC enclosures

HDC IP68 16B SS 2M40

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	80 mm	Width (inches)	3.15 inch
Height	111.5 mm	Height (inches)	4.39 inch
Mounting dimension - width	160 mm	Mounting dimension - height	60 mm
Net weight	1,029 g		

Temperatures

Limit temperature	-50 °C ... 125 °C
-------------------	-------------------

Dimensions

Cable entry	w. threading	Height of housing B	111.5 mm
Hole pitch length A2	160 mm	Total length housing	189 mm

General data

EMC housings	Yes	Housing main material	diecast aluminium
Protection degree	IP68, IP69K	Surface finish	Powder coating

Version

Cable entry	w. threading	Clamp version	Screw plug
Design	Standard	Design of housing	Base enclosure
Design of locking system	Screw plug	Internal thread	M 40
Number of cable entry on top	0	Number of cable entry sideways	2
Sealing	Silicone rubber	Size	6
Size of cable entries	M 40	Suitable for ModuPlug®	Yes
Top part/bottom part/lid	lower part	Type	Base housing

Classifications

ETIM 3.0	EC000437	ETIM 4.0	EC000437
ETIM 5.0	EC000437	ETIM 6.0	EC000437
UNSPSC	30-21-18-01	eClass 5.1	27-14-34-19
eClass 6.2	27-14-34-19	eClass 7.1	27-44-05-15
eClass 8.1	27-44-05-15	eClass 9.0	27-44-02-02
eClass 9.1	27-44-02-02		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN FL FIELDWIRING EN
Engineering Data	EPLAN
Engineering Data	STEP

Creation date May 27, 2019 9:45:58 PM CEST

HDC enclosures HDC IP68 16B SS 2M40

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

