

HDC enclosures HDC IP68 10B TSS 1PG29

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The new RockStar® enclosures are resistant to seawater and offer a high degree of shock resistance, meet IP 68 and IP 69K, and have been developed for use under extreme environmental conditions and designed for the high vibration requirements acc. to DIN EN 61373 cat. 2 (bogie). As such, this housing family is ideally suited for fault- and maintenance-free operation of heavy-duty connectors in transport and traffic engineering as well as in power engineering and in applications with extreme requirements. During development, measures were also implemented to make the enclosures extremely EMC-resistant.

General ordering data

Type	HDC IP68 10B TSS 1PG29
Order No.	1082680000
Version	HDC enclosures, Size: 4, Protection degree: IP68, IP69K, Plug housing, Screw plug, Standard, Size of cable entries: PG 29
GTIN (EAN)	4032248846009
Qty.	1 pc(s).

**HDC enclosures
HDC IP68 10B TSS 1PG29**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data
Dimensions and weights

Width	58 mm	Width (inches)	2.283 inch
Height	100.5 mm	Height (inches)	3.957 inch
Depth	144 mm	Depth (inches)	5.669 inch
Net weight	475 g		

Temperatures

Limit temperature	-50 °C ... 125 °C
-------------------	-------------------

Dimensions

Cable entry	w. threading	Total length housing	144 mm
-------------	--------------	----------------------	--------

General data

EMC housings	Yes	Housing main material	diecast aluminium
Material of locking element	Stainless steel, rust-proof	Protection degree	IP68, IP69K
Surface finish	Powder coating	Tightening torque	6.5 Nm

Version

Cable entry	w. threading	Clamp version	Screw plug
Design	Standard	Design of housing	Plug housing
Design of locking system	Screw plug	Internal thread	PG 29
Number of cable entry on top	0	Number of cable entry sideways	1
Size	4	Size of cable entries	PG 29
Suitable for ModuPlug®	Yes	Tightening torque	6.5 Nm
Top part/bottom part/lid	upper part	Type	Plug

Classifications

ETIM 3.0	EC000437	ETIM 4.0	EC000437
ETIM 5.0	EC000437	ETIM 6.0	EC000437
UNSPSC	30-21-18-01	eClass 5.1	27-14-34-19
eClass 6.2	27-14-34-19	eClass 7.1	27-44-05-15
eClass 8.1	27-44-05-15	eClass 9.0	27-44-02-02
eClass 9.1	27-44-02-02		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN FL FIELDWIRING EN
Engineering Data	EPLAN
Engineering Data	STEP

Creation date May 27, 2019 9:47:18 PM CEST

Data sheet

**HDC enclosures
HDC IP68 10B TSS 1PG29**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

