

European Region

Download Instructions (multilingual)

[Page 01](#) | [Page 02](#)

Universal Charger

INNOVATIVE

- Unique and modern design
- Charges AA, AAA, C, D and 9V NiMH rechargeable batteries.



SMART

- LCD panel indicating charging status
- LED indicator for 9V



POWERFUL

- 3-5 hour charging time



Before Using Your Charger:

Please read all instructions and cautionary markings on the battery charger, batteries, and device.

Product Detail:

Designation: Universal Charger - European Region

Color: Black and Silver

Charging Current: 2 or 4 "AA-C-D" 650mA

2 or 4 "AAA" 400mA 1 or 2 "9V" 17mA

Trickle Charge: "AA-C-D" 50mA

"AAA" 25mA

Battery (NiMH)	Capacity (mAh)	Estimated (time)
AA	2500-2650	4.5-5.0 hrs
AA	1700-2400	3.0-4.5 hrs
AAA	850-1000	2.5-3.0 hrs
C/D	2500	4.5 hrs
9V	175	12.5 hrs

Shutoff Mechanism: Delta V Detection and Timer Control

Delta V Detection 5mV per cell for "AA-AAA-C-D"

Max Timer Control 2 or 4 "AA-C-D" 5 hours

2 or 4 "AA" 3.5 hours

Charger Input : DC 12V, 600mA

AC Adapter Input: 100-240V AC 50/60Hz 190mA

AC Adapter Output: DC 12V, 600mA

Weight (charger): 322 grams

Dimensions (mm): 65 x 180 x 130 (H x L x W)

Safety Features: Delta V Charging Cut Off

Short Circuit and Reverse Polarity Protection

Safety Timer to Prevent Over Charge

Bad Battery Detection

NOTE: Batteries must be charged in pairs with the exception of "9V" batteries that can be charged individually

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication.

©Energizer

Contents herein do not constitute a warranty.