

[Download Instructions \(Americas\)](#)
[Download Instructions \(Rest of World\)](#)

Product Detail:

Designation: Value Charger / Maxi Charger

Model: CHVCM4E / CHVCM4

Color: Black

Charge Capability: "AA" (2) or (4) / "AAA" (2) or (4)
 "AA" (2) and "AAA" (2) Simultaneously

Note: Please note battery orientation diagrams in the instructions.

Charging Times: (estimated)	Battery (NiMH)	Capacity (mAh)	Estimated (time)
	AA	1300-2000	6-8 hrs
	AA	2000-2300	8-10 hrs
	AAA	500-800	5-7 hrs

Shutoff Mechanism: Delta V Detection

Timer Control: 11 hours

Charging Current: "AA" 260-300mA

"AAA" 120-150mA

Trickle Charge: None

Input Rating (US): 110-127VAC, 50-60Hz, 6W

Input Rating: 100-240VAC, 50-60Hz, 6W

Typical Weight: 107 grams

Dimensions (mm): 115 x 71 x 62 (H x L x W)

Safety Features: Reverse Polarity Protection

Bad Battery Detection

Primary Battery Detection

Delta V Charging Cut Off

Safety Timer to Prevent Overcharge

ENHANCED COMMUNICATION

- Multiple colored LED lights indicate charge status



BATTERY PROTECTION

- Limits damage to batteries from overcharge



SAFETY TIMER

- Ensures charger is not active for extended periods of time



Before Using Your Charger:

Please read all instructions and cautionary markings on the battery charger, batteries, and device.

Best used with Energizer® NiMH batteries.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication.

Contents herein do not constitute a warranty.