

HTF HYB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- for C1 contacts
- for D-Sub contact of CM-20 ConCept Module
- IE crimping tool

General ordering data

Type	HTF HYB
Order No.	1119580000
Version	0.08mm², 1mm², FoderBcrimp
GTIN (EAN)	4032248900626
Qty.	1 pc(s).

HTF HYB

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	200 mm	Weight	438 g
Net weight	443.2 g		

Contact description

Crimping range, min.	0.08 mm ²	Crimping range, max.	1 mm ²
----------------------	----------------------	----------------------	-------------------

Tool data - crimping

Crimping profile 1, min.	0.08 mm ²	Crimping typerofile	FoderBcrimp
Crimping profile 1, max.	0.2 mm ²	Crimping profile 2, min.	0.2 mm ²
Crimping profile 2, max.	0.5 mm ²	Crimping profile 3, min.	0.75 mm ²
Crimping profile 3, max.	1 mm ²		

Classifications

ETIM 3.0	EC001396	UNSPSC	27-11-27-20
eClass 5.1	21-05-08-01	eClass 6.2	21-04-38-90
eClass 7.1	21-05-08-04		

Approvals

Approvals	
ROHS	Conform