

**Cutting tools
KT 22**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Cutting tools for wires up to 8 mm, 12 mm or 20 mm outer diameter.
The special cutting shape allows for pinch-free cutting of copper and aluminium wires.

General ordering data

Type	KT 22
Order No.	1157830000
Version	Cutting tools ,Cutting tool for one-hand operation
GTIN (EAN)	4032248945528
Qty.	1 pc(s).

**Cutting tools
KT 22**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	210 mm	Width	66 mm
Height	30 mm	Weight	460 g
Net weight	471.68 g		

Technical data

Version One-hand mechanical

Data, telephone and control cable

Data telephone control cable, max. Ø 22 mm

max. Cutting performance - aluminium cable

Single-core aluminium cable, max.(mm ²)	50 mm ²	Stranded aluminium cable, max (mm ²)	70 mm ²
Stranded aluminium cable, max. (AWG)	2/0	Stranded aluminium cable, max. diameter	22 mm

max. Cutting performance - copper cable

Copper cable - flexible, max.	95 mm ²	Copper cable - flexible, max. (AWG)	3/0
Copper cable - solid, max.	25 mm ²	Copper cable - solid, max. (AWG)	3
Copper cable - stranded, max.	50 mm ²	Copper cable - stranded, max. (AWG)	1
Copper cable, max. diameter	22 mm		

Classifications

ETIM 3.0	EC000005	UNSPSC	31-16-31-02
eClass 5.1	27-40-02-01	eClass 6.2	21-04-90-90
eClass 7.1	27-40-02-01		

Product information

Descriptive text technical data Tool closed

Approvals

Approvals




ROHS Conform


Datenblatt


**Cutting tools
KT 22**


Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

 max. 22 mm

 max. 25 mm²

 max. 50 mm²

 max. 95 mm²
