

PB-DP SUB-D ZF TERM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

General ordering data

Type	PB-DP SUB-D ZF TERM
Order No.	1161870000
Version	
GTIN (EAN)	4032248950706
Qty.	1 pc(s).

PB-DP SUB-D ZF TERM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 91 g

Technical specifications for sub-D connector

Data rate	12 Mbit/s	Housing main material	ZnAl
Humidity	Max. 75% at +25°C, non-condensing	Interlock	UNC4-40
Outgoing elbow	90°	PROFIBUS DP interface	D-Sub 9-pole, Pin
PROFIBUS cable interface	Tension clamp connection	Plug-in connector and pin assignment	In accordance with the PROFIBUS specification
Plugging cycles	≥ 200	Protection degree	IP 30
Temperature range of housing	-20...+70 ° C		

Classifications

eClass 6.2 27-26-07-07 eClass 7.1 27-44-03-07

Approvals

ROHS Conform