

**SAIE-M12B-5S2.0U HW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

**General ordering data**

Type	SAIE-M12B-5S2.0U HW
Order No.	<a href="#">1222270000</a>
Version	Built-in plugs, M12, PG 9, No. of poles: 5, 2 m
GTIN (EAN)	4050118005905
Qty.	1 pc(s).

## SAIE-M12B-5S2.0U HW

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Net weight	38 g
------------	------

### General data

Cable gland	PG 9	Cable length	2 m
Conductor O.D.	-	Contact surface	Gold-plated
Contact tube diameter	M12	Core cross-section	0.25 mm <sup>2</sup>
Housing main material	Zinc diecast, nickel-plated	Material	PUR/ PVC
No. of poles	5	Protection degree	IP 68
Rated current	4 A	Rated current	4 A (5-pole), 2 A (8-pole)
Rated voltage	125 V	Rated voltage (text)	125 V (5-pole) / 60 V (8-pole)
Sheathing colour	Black	Strand cable length	2 m
Temperature range of housing	-5 ... +70 °C		

### Classifications

eClass 6.2	27-26-07-02
------------	-------------

### Approvals

ROHS	Conform
------	---------