SAIE-M12B-8S2.0U HW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Type	SAIE-M12B-8S2.0U HW
Order No.	1223650000
Version	Built-in plugs, M12, PG 9, No. of poles: 8, 2 m
GTIN (EAN)	4050118007305
Qty.	1 pc(s).

SAIE-M12B-8S2.0U HW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	48 g

General data

Cable gland	PG 9	Cable length	2 m
Conductor O.D.	-	Contact surface	Gold-plated
Contact tube diameter	M12	Core cross-section	0.25 mm²
Housing main material	Zinc diecast, nickel-plated	Material	PUR/ PVC
No. of poles	8	Protection degree	IP 68
Rated current	2 A	Rated current	4 A (5-pole), 2 A (8-pole)
Rated voltage	60 V	Rated voltage (text)	125 V (5-pole) / 60 V (8-pole)
Sheathing colour	Black	Strand cable length	2 m
Temperature range of housing	-5 ... +70 °C		

Classifications

eClass 6.2	27-26-07-02

Approvals

ROHS	Conform