

**Industrial Ethernet  
EBR-MODULE RS232**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**External module for backing up and restoring the configuration**

- Reduced system downtime by simple reconfiguration if equipment is swapped over
- Plug&Play system backup and recovery
- Compact and robust design
- Can be used with all Weidmüller Managed Switches in the Value and PremiumLine as well as the Weidmüller WLAN Access Point

**General ordering data**

Type	EBR-MODULE RS232
Order No.	<a href="#">1241430000</a>
Version	Configuration module, IP 40, 0 °C...+60 °C
GTIN (EAN)	4050118029086
Qty.	1 pc(s).

## Industrial Ethernet EBR-MODULE RS232

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Width	32.5 mm	Height	12 mm
Depth	97 mm	Weight	50 g
Net weight	50 g		

### EMC conformity and approvals

EMC standards	FCC Part 15, CISPR (EN55022) Class A, EN 61000-4-2 (ESD), Stage 2, EN 61000-4-3 (RS), Stage 3, EN 61000-4-4 (EFT), Stage 3, EN 61000-4-5 (surge voltage), Stage 3, EN 61000-4-6 (CS), Stage 3
---------------	---

### Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	60 °C
Operating temperature, min.	0 °C	Storage temperature, max.	70 °C
Storage temperature, min.	-20 °C		

### Guarantee

Time interval	5 years
---------------	---------

### Order data

Operating temperature	0 °C...+60 °C
-----------------------	---------------

### Power supply

Connection type	RJ45-Port, RS232	Input voltage	3 to 5 V DC (via the RTS signal of the RS-232 port)
-----------------	------------------	---------------	---

### Technical data

Cable length	0.35 m	Housing main material	PVC casting
Protection degree	IP 40	Type of fixing	M4 screw (<4 mm)

### Classifications

eClass 6.2	19-17-01-06	eClass 7.1	19-17-01-06
------------	-------------	------------	-------------

### Approvals

ROHS	Conform
------	---------

### Downloads

Package insert	<a href="#">Hardware Installation Guide</a>
Declaration of Conformity	<a href="#">K424_01_11.pdf</a>
	<a href="#">3D Modell</a>