

CRIMPFIX L PZ3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Orders on request only



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Type	CRIMPFIX L PZ3
Order No.	1243790000
Version	Automatic machines, Automatic stripper and crimper
GTIN (EAN)	4050118031966
Qty.	1 pc(s).

CRIMPFIX L PZ3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Width	390 mm	Width (inches)	15.354 inch
Height	460 mm	Height (inches)	18.11 inch
Depth	330 mm	Depth (inches)	12.992 inch
Weight	31 kg	Net weight	34,000 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Technical data

Electrical connection 100-240 V / 50/65 Hz

PW65 maintenance - automatic stripping/crimping

Compressed-air connection	5 bar	Consumables	loose wire-end ferrules
Crimping length	8 mm	Drive	Electropneumatic
Electrical connection	100-240 V / 50/65 Hz	Length of wire-end ferrule	14 mm
Pulse time	approx. 1 s	Stripping range	0.5 - 2.5 mm ²
Wire end ferrules cross-section, max.	2.5 mm ²	Wire end ferrules cross-section, min.	0.5 mm ²

Classifications

ETIM 4.0	EC000149	ETIM 5.0	EC000149
ETIM 6.0	EC002778	eClass 6.2	17-13-01-01
eClass 8.1	21-04-04-90	eClass 9.0	17-13-01-01
eClass 9.1	17-13-01-01		

Approvals

Approvals



ROHS

Conform

DownloadsUser Documentation [Manual](#)