

SAI-6-S12 4P M12 L**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



M12 distributors are available in various versions. The 4, 6 or 8 M12 slots are in 4 or 5 pole design. The group outlet is designed as a fixed cable version, hood version for connection by the user, or with M23. Special versions are also available. For instance, there are 1-to-1 distributors for use with any connection types, or distributors approved for Ex Zone 1.

General ordering data

Type	SAI-6-S12 4P M12 L
Order No.	1265940000
Version	Sensor-actuator passive distributor, M12, with M12 outlet, 12-pole, A-coded, Yes
GTIN (EAN)	4050118055641
Qty.	1 pc(s).

SAI-6-S12 4P M12 L**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	148 g
------------	-------

Temperatures

Operating temperature, max.	80 °C	Operating temperature	- 80°C
-----------------------------	-------	-----------------------	--------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Connection data

Distributor outlet	with M12 outlet, 12-pole, A-coded
--------------------	--------------------------------------

Standards

Certificate No. (cURus)	E92202
-------------------------	--------

Electrical data

Rated voltage , min.	10 V	Rated voltage , max.	30 V
Max. current-carrying capacity per slot	2 A	Total current	6 A
Current per signal	1 A		

General technical data

Protection degree	IP67	No. of poles	4
Number of contact sockets	6	Connection thread	M12
Pollution severity	3	Fire behaviour	V-0
LED	Yes		

Material data

Housing main material	Pocan	Housing colour	grey, RAL 7032
Screw socket	Nickel-plated CuZn	Contact material	CuZn
Contact surface	Gold-plated	Contact carrier material	PBT (UL 94 V0)

Technical data cable

No. of poles	4
--------------	---

Classifications

ETIM 4.0	EC002585	ETIM 5.0	EC002585
ETIM 6.0	EC002585	eClass 6.2	27-06-91-90
eClass 7.1	27-06-91-90	eClass 8.1	27-06-91-90
eClass 9.0	27-44-01-08	eClass 9.1	27-44-01-08

SAI-6-S12 4P M12 L

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Downloads

Brochure/Catalogue

[CAT 8 SAI 15/16 EN](#)
[FL FIELDWIRING EN](#)