

**Industrial Ethernet
IE-SFP-1GLSXLC-T****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- IEEE 802.3z-compliant (Gigabit modules)
- IEEE 802.3u-compliant (Fast Ethernet modules)
- Symmetric LVPECL I/Os (Gigabit modules)
- Symmetric PECL I/Os (Fast Ethernet modules)
- TTL signal detection indicator
- In operation insertable duplex LC connector
- Class 1 laser product, EN60825-1 compliant
- -40 to 85°C operating temperature (T models)

General ordering data

Type	IE-SFP-1GLSXLC-T
Order No.	1286710000
Version	SFP-Modul, -40 °C...+85 °C, Gigabit-Ethernet, Multimode, LC connectors, 2 km
GTIN (EAN)	4050118077520
Qty.	1 pc(s).

Industrial Ethernet IE-SFP-1GLSXLC-T

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	25 g
------------	------

EMC conformity and approvals

Security	UL, TÜV
----------	---------

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	85 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Guarantee

Time interval	3 years
---------------	---------

Interfaces

Ethernet ports	1	Plug-in connector	Duplex-LC
----------------	---	-------------------	-----------

Order data

Operating temperature	SFP alternatives	Gigabit-Ethernet, Multimode, LC connectors, 2 km
-40 °C...+85 °C		

Classifications

eClass 6.2	19-17-01-90	eClass 7.1	19-17-01-90
------------	-------------	------------	-------------

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Declaration of Conformity	K4230912.pdf
---------------------------	------------------------------