

**Industrial Ethernet
IE-SFP-1GLHXLC-T**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



- IEEE 802.3z-compliant (Gigabit modules)
- IEEE 802.3u-compliant (Fast Ethernet modules)
- Symmetric LVPECL I/Os (Gigabit modules)
- Symmetric PECL I/Os (Fast Ethernet modules)
- TTL signal detection indicator
- In operation insertable duplex LC connector
- Class 1 laser product, EN60825-1 compliant
- -40 to 85°C operating temperature (T models)

General ordering data

Type	IE-SFP-1GLHXLC-T
Order No.	1286730000
Version	SFP-Modul, -40 °C...+85 °C, Gigabit-Ethernet, Singlemode, LC connectors, 40 km
GTIN (EAN)	4050118077728
Qty.	1 pc(s).

**Industrial Ethernet
IE-SFP-1GLHXLC-T**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 25 g

EMC conformity and approvals

Security UL, TÜV

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	85 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Guarantee

Time interval 3 years

Interfaces

Ethernet ports 1 Plug-in connector Duplex-LC

Order data

Operating temperature -40 °C...+85 °C SFP alternatives Gigabit-Ethernet, Singlemode, LC connectors, 40 km

Classifications

eClass 6.2 19-17-01-90 eClass 7.1 19-17-01-90

Approvals

Approvals



ROHS Conform

Downloads

Declaration of Conformity [K4230912.pdf](#)