

SAIE-7/8"S-4-0.2U-PG11**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Similar to illustration

Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Type	SAIE-7/8"S-4-0.2U-PG11
Order No.	1292400000
Version	Built-in plugs, 7/8", PG 11, No. of poles: 4, 0.2 m
GTIN (EAN)	4050118088533
Qty.	1 pc(s).

SAIE-7/8"S-4-0.2U-PG11

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 43 g

General data

Cable gland	PG 11	Cable length	0.2 m
Conductor O.D.	-	Contact material	CuZn
Contact surface	Gold-plated	Contact tube diameter	7/8"
Core cross-section	0.75 mm ²	Housing main material	Zinc diecast, nickel-plated
Material	PUR/ PUR	No. of poles	4
Plugging cycles	≥ 100	Protection degree	IP 67
Rated current	8 A	Rated current	8 A (4- and 5-pole), 10 A (3-pole)
Rated voltage	300 V	Strand cable length	0.2 m
Temperature range of housing	-25...+85 °C	Type of connection	Pin

Classifications

eClass 6.2 27-26-07-02 eClass 7.1 27-44-01-02

Approvals

Approvals



ROHS Conform

SAIE-7/8"S-4-0.2U-PG11

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Zeichnungen

