

**Industrial Ethernet  
IE-C6FP8LD0050X40X40-Y**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Similar to illustration

Assembled IE cables, patch cable crossover, Cat. 6, LSZH,  
grey

**General ordering data**

Type	IE-C6FP8LD0050X40X40-Y
Order No.	<a href="#">1312160050</a>
Version	Patch cable, crossover, RJ45 IP 20, RJ45 IP 20, Cat.6 <sub>A</sub> / Class E <sub>A</sub> (ISO/IEC 11801 2010), LSZH, 5 m
GTIN (EAN)	4050118114799
Qty.	1 pc(s).

**Industrial Ethernet  
IE-C6FP8LD0050X40X40-Y**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Length	5 m	Length (inches)	0.197 inch
Net weight	199 g	Insulation cross-section	1.04 mm

**Temperatures**

Operating temperature, max.	60 °C	Operating temperature, min.	-20 °C
Storage temperature, max.	60 °C	Storage temperature, min.	-20 °C
Operating temperature	-20 °C...60 °C	Storage temperature	-20 °C...60 °C
Installation temperature	0 °C...50 °C		

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Electrical properties**

Current-carrying capacity at 50 °C	1 A	Operating voltage	48 V AC / DC
PoE / PoE+	conforming to IEEE 802.3at		

**Standards**

Application-specific communication cable facilities	ANSI / TIA / EIA-568-B.2-10, ISO / IEC 11801:2002, EN50173-1:2007	Connector standard	IEC 60603-7-51
Certificate no. (cULus)	E316369		

**Cable structure**

Copper diameter	0.43 mm	Strands	7
Cross-section	4*2*AWG 27/7 - 4*2*0.1 mm <sup>2</sup>	Insulation	PE
Insulation cross-section	1.04 mm	No. of wires	8
Arrangement of wire cores	Twisted pair	Colour sequence or wires - wire pairs	white - blue, white - orange, white - green, white - brown
Shielding	S/FTP	Complete shielding	Shielding braid made from copper wiring
Overlap of shielding braid	60 %	Material sheath	LSZH
Sheath diameter, min.	5.5 mm	Sheath diameter, max.	5.9 mm
Sheathing colour	light grey (RAL 7035)		

**Electrical properties of cable**

Category	Cat.6A / Class E <sub>A</sub> (ISO/IEC 11801 2010)	Operating voltage	48 V AC / DC
Operating voltage (UL rating)	30 V AC / 42.4 V DC	Test voltage: wire-wire-shield	750 V DC, 1 min
Characteristic impedance	100 ± 15 Ω at 1-100 MHz	Deviation	25 ns/100m
Resistance differential	5 %	Capacity at 1 kHz	46 nF/km
Speed	10 GBit/s	Coupling resistance at 10 MHz	5 mΩ/m
Shield attenuation up to 1000 MHz	60 dB	Coupling attenuation up to 1000 MHz	80 dB
Separating class according to EN 50174-2	d		

Creation date May 27, 2019 10:42:16 PM CEST

Catalogue status 23.05.2019 / We reserve the right to make technical changes.

**Industrial Ethernet  
IE-C6FP8LD0050X40X40-Y**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Mechanical and material properties of cable**

Min. bending radius, once only	25 mm	Min. bending radius, repetitive	50 mm
Speed	10 GBit/s	Resistance to spread of flame	in accordance with IEC 60332-1 / UL 1581 FT2
Halogen	halogen-free, according to IEC 60754-2		

**plug**

Connector left	RJ45 IP 20	Connector right	RJ45 IP 20
----------------	------------	-----------------	------------

**Classifications**

ETIM 3.0	EC001262	ETIM 5.0	EC000830
ETIM 6.0	EC002599	UNSPSC	26-12-16-09
eClass 5.1	27-06-18-01	eClass 6.2	27-06-18-01
eClass 7.1	27-06-18-01	eClass 8.1	27-06-18-01
eClass 9.0	27-06-03-08	eClass 9.1	27-06-03-08

**Approvals**

Approvals



ROHS Conform

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">DUXR.E316369</a>
Brochure/Catalogue	<a href="#">CAT 9 IETH 15/16 EN</a> <a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a>
Product Change Notification	<a href="#">PCN-PB47-20180213-00-A_EN</a> <a href="#">PCN-PB47-20180213-00-A_DE</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>

**Data sheet**

**Industrial Ethernet  
IE-C6FP8LD0050X40X40-Y**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Drawings**

**Wiring**



**Dimensioned drawing**

