# Device markers
# THM MT30X 17.5/17.5 SI

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The ThermoMark labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

## General ordering data

| | |
|---|---|
| Type | THM MT30X 17.5/17.5 SI |
| Order No. | 1338280000 |
| Version | Device markers, Label, 17.5 x 17.5 mm, Polyester film, Colour: Silver |
| GTIN (EAN) | 4050118142839 |
| Qty. | 1 pc(s). |

# Device markers
# THM MT30X 17.5/17.5 SI

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

## Technische Daten

### Dimensions and weights

| | | | |
|---|---|---|---|
| Length | 17.5 mm | Width | 17.5 mm |
| Net weight | 430 g | | |

### General data

| | | | |
|---|---|---|---|
| Adhesive | Acrylate adhesive | Colour | Silver |
| Material | Polyester film | Number per roll | 5,000 |
| Number per sheet | 5,000 | Operating temperature range, max. | 150 °C |
| Operating temperature range, min. | -40 °C | Printing method | Thermotransfer |
| UL 94 flammability rating | HB | UL 969 flammability rating | Yes |

### Classifications

| | |
|---|---|
| eClass 6.2 | 27-14-91-29 |

### Approvals

| | |
|---|---|
| ROHS | Conform |

### Downloads

| | |
|---|---|
| M-Print® PRO configuration file | lab_thm_mt_30_17-5_17-5_mcf.zip |