

**HDC enclosures
HDC 07A DODL 2B0****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 07A DODL 2B0
Order No.	1665760000
Version	HDC enclosures, Size: 1, Protection degree: IP65, Cover for lower part of housing, Side-locking clamp on lower side, Standard
GTIN (EAN)	4008190422783
Qty.	1 pc(s).

HDC enclosures HDC 07A DODL 2B0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	36.5 mm	Width (inches)	1.437 inch
Height	17.5 mm	Height (inches)	0.689 inch
Depth	26.8 mm	Depth (inches)	1.055 inch
Net weight	7 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Dimensions

Cable entry	for male insert	Height of housing B	17.5 mm
Total length housing	26.8 mm	Width housing C	26.8 mm

General data

EMC housings	No	Housing main material	Plastic
Protection degree	IP65	UL 94 flammability rating	V-0

Version

Cable entry	for male insert	Clamp version	Side-locking clamp
Design	Standard	Design of housing	Cover for lower part of housing
Design of locking system	Side-locking clamp on lower side	Size	1
Suitable for ModuPlug®	No	Top part/bottom part/lid	Cover
Type	Cover		

Classifications

ETIM 3.0	EC000437	ETIM 4.0	EC000437
ETIM 5.0	EC000437	ETIM 6.0	EC000437
UNSPSC	30-21-18-01	eClass 5.1	27-14-34-19
eClass 6.2	27-26-12-03	eClass 7.1	27-44-02-02
eClass 8.1	27-44-02-02	eClass 9.0	27-44-02-02
eClass 9.1	27-44-02-02		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN FL FIELDWIRING EN
Engineering Data	EPLAN.WSCAD
Engineering Data	1665760000_HDC_07A_DODL_2B0_STP.dxf STEP
Technical Documentation	1665760000_HDC_07A_DODL_2B0_STP_Blatt_1.pdf

Creation date May 27, 2019 10:53:04 PM CEST

HDC enclosures HDC 07A DODL 2B0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

