

## HDC enclosures HDC 32A ABU

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

### General ordering data

Type	HDC 32A ABU
Order No.	<a href="#">1665860000</a>
Version	HDC enclosures, Size: 7, Protection degree: IP65, Bulkhead enclosure, Side-locking clamp on lower side, Standard
GTIN (EAN)	4008190871253
Qty.	1 pc(s).

# Data sheet

## HDC enclosures HDC 32A ABU

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	60.5 mm	Width (inches)	2.382 inch
Height	30 mm	Height (inches)	1.181 inch
Mounting dimension - width	92 mm	Mounting dimension - height	42 mm
Net weight	176 g		

### Temperatures

Limit temperature -40 °C ... 125 °C

### Environmental Product Compliance

REACH SVHC Lead 7439-92-1

### Dimensions

Height of base B1	7 mm	Height of housing B	30 mm
Hole pitch length A2	92 mm	Total length housing	82 mm
Width base C1	60.5 mm	Width housing C	56 mm

### General data

EMC housings	No	Housing main material	diecast aluminium
Material of locking element	Stainless steel, rust-proof	Protection degree	IP65
Surface finish	Powder coating		

### Version

Clamp version	Side-locking clamp	Design	Standard
Design of housing	Bulkhead enclosure	Design of locking system	Side-locking clamp on lower side
Sealing	NBR	Size	7
Suitable for ModuPlug®	No	Top part/bottom part/lid	lower part
Type	Bulkhead (feed-through)		

### Classifications

ETIM 3.0	EC000437	ETIM 4.0	EC000437
ETIM 5.0	EC000437	ETIM 6.0	EC000437
UNSPSC	30-21-18-01	eClass 5.1	27-14-34-19
eClass 6.2	27-26-12-03	eClass 7.1	27-44-02-02
eClass 8.1	27-44-02-02	eClass 9.0	27-44-02-02
eClass 9.1	27-44-02-02		

### Approvals

Approvals



ROHS

Conform

**HDC enclosures  
HDC 32A ABU**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data****Downloads**

---

Brochure/Catalogue	<a href="#">CAT 3 HDC 17/18 EN</a> <a href="#">FL FIELDWIRING EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>
Engineering Data	<a href="#">1665860000 HDC 32A ABU_STP.dxf</a> <a href="#">STEP</a>
Technical Documentation	<a href="#">1665860000 HDC 32A ABU_STP_Blatt_1.pdf</a>

---