

**Cable glands
ADAP EX M63-M50**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The range of cable glands is rounded off by a large number of accessories.

Adaptors serve as connection pieces between threaded holes and cable glands with differing thread sizes and types.

General ordering data

Type	ADAP EX M63-M50
Order No.	1738190000
Version	Adaptor, Brass, nickel-plated, M 63, M 50, metric, IP 54
GTIN (EAN)	4008190958084
Qty.	1 pc(s).

**Cable glands
ADAP EX M63-M50**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten**Dimensions and weights**

Net weight	253 g
------------	-------

Approvals

Approval for cable gland	II 2 GD, Ex d IIC, Ex e II, Ex tD
--------------------------	-----------------------------------

General information

Cable gland	metric	External thread	M 63
Internal thread	M 50	Material	Brass, nickel-plated
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5	Protection degree with GWDR	IP 54

Classifications

ETIM 3.0	EC000441	UNSPSC	30-21-18-01
eClass 5.1	27-14-92-01	eClass 6.2	27-14-91-11
eClass 7.1	27-14-91-11		

Product information

Descriptive text ordering data	Qty. = 1
Descriptive text accessories	For gland fitting tools see the chapter "Tools", p. N.81

Approvals

ROHS	Conform
------	---------