

Device markers
THM MT30X 38/19 SI/M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The ThermoMark labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

General ordering data

Type	THM MT30X 38/19 SI/M
Order No.	1751800001
Version	Device markers, Label, 38 x 19 mm, Polyester film, Colour: Silver
GTIN (EAN)	4032248001569
Qty.	1 pc(s).

Device markers THM MT30X 38/19 SI/M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	38 mm	Width	19 mm
Net weight	270 g		

General data

Adhesive	Acrylate adhesive	Colour	Silver
Material	Polyester film	Number per roll	2,000
Number per sheet	2,000	Operating temperature range, max.	150 °C
Operating temperature range, min.	-40 °C	Printing method	Thermotransfer
UL 94 flammability rating	HB	UL 969 flammability rating	Yes

Classifications

ETIM 3.0	EC001288	UNSPSC	30-21-18-01
eClass 5.1	27-14-91-29	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

Approvals

Approvals	
ROHS	Conform

Downloads

M-Print® PRO configuration file	lab_thm_mt_30_38_19_mcf.zip
---------------------------------	---