

Plotterpen 0,25**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The M-Print® PRO printing and ordering software for markers and labels® is a professional Windows-based solution for both printing and ordering Weidmüller labels and markers. This software allows you to optimise the process of identifying electrical equipment. You can design, label and order your marking materials easily, professionally and quickly: with text, frames, lines, graphics, bar codes, serial numbers and photos.

- Integrated product catalogue for all labels and markers, including illustrations, link to the website and product data sheet
- Markers and labels can be designed on as many levels as required
- Customised formatting of individual text characters (RTF)
- Copy and paste texts and their formats
- Supports UNICODE for foreign-language text such as Russian, Chinese, Polish, etc.
- Data entry in labels and spreadsheets, or directly in Microsoft Excel
- Numeric and alpha-numeric counters and sequences
- Extensive range of image formats (*.bmp, *.wmf, *.png, *.ico, *.jpeg, *.jpg, *.tif, *.gif)
- Image library including symbols used in electrical engineering
- Option of assigning products to the selected printer

- Output devices supported: PrintJet I+II, SMarkLaser, ThermoCard, THM, plus standard printers with Windows drivers
- Online update service via the internet
- RailDesigner interface
- Import wizard for file formats such as *.txt, *.csv, *.xml, etc.
- Transfer of data from CAE systems

General ordering data

Type	Plotterpen 0,25
Order No.	1768540000
Version	Plotter pen
GTIN (EAN)	4032248110797
Qty.	1 pc(s).

Plotterpen 0,25**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com**Technische Daten****Dimensions and weights**

Net weight	6.5 g
------------	-------

Classifications

UNSPSC	81-11-18-12	eClass 5.1	19-03-90-90
eClass 6.2	19-14-92-90	eClass 7.1	19-14-92-90

Approvals

Approvals

ROHS	Conform
------	---------