

**Cable markers  
THM WRITE ON 25/76 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality THM Plus S thermal transfer printer

**General ordering data**

|            |                                                                 |
|------------|-----------------------------------------------------------------|
| Type       | THM WRITE ON 25/76 WS                                           |
| Order No.  | <a href="#">1774350000</a>                                      |
| Version    | Cable markers, Label, 76 x 25 mm, Polyester film, Colour: White |
| GTIN (EAN) | 4032248148530                                                   |
| Qty.       | 1 pc(s).                                                        |

## Cable markers THM WRITE ON 25/76 WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Dimensions and weights

|        |        |            |       |
|--------|--------|------------|-------|
| Length | 76 mm  | Width      | 25 mm |
| Depth  | 0.5 mm | Net weight | 656 g |

### General data

|                                   |                   |                                              |            |
|-----------------------------------|-------------------|----------------------------------------------|------------|
| Adhesive                          | Acrylate adhesive | Colour                                       | White      |
| Material                          | Polyester film    | Material colour according to resistance code | 9          |
| Number per roll                   | 1,800             | Operating temperature range, max.            | 150 °C     |
| Operating temperature range, min. | -40 °C            | Size of labelling field                      | 25 x 15 mm |
| Type of printing                  | blank             | UL 94 flammability rating                    | HB         |
| UL 969 flammability rating        | Yes               |                                              |            |

### Conductor and cable markers

|                      |         |                      |      |
|----------------------|---------|----------------------|------|
| Conductor O.D., max. | 14.1 mm | Conductor O.D., min. | 0 mm |
|----------------------|---------|----------------------|------|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001530    | UNSPSC     | 44-12-17-08 |
| eClass 5.1 | 27-14-91-03 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 |            |             |

### Approvals

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |

### Downloads

|                                 |                                                |
|---------------------------------|------------------------------------------------|
| M-Print® PRO configuration file | <a href="#">lab_thm_write_on_25_76_mcf.zip</a> |
|---------------------------------|------------------------------------------------|