

SAIS-4-IDC M12 small**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The IDC is simple and quick to assemble since this technology allows the conductor to be inserted directly into the terminal point, without crimping or having to strip the insulation. It also has excellent functional security.

General ordering data

Type	SAIS-4-IDC M12 small
Order No.	1781550001
Version	Sockets prefabricated to customer spec., Plugs prefabricated to customer spec., M12, pin, straight
GTIN (EAN)	4032248429950
Qty.	1 pc(s).

SAIS-4-IDC M12 small

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Width	15.3 mm	Net weight	22.9 g
-------	---------	------------	--------

Technical data customisable plug-in connectors

Cable diameter	4...5.1 mm	Cable diameter, max.	5.1 mm
Cable diameter, min.	4 mm	Coding	A
Connection cross-section, max.	0.34 mm ²	Connection cross-section, min.	0.14 mm ²
Contact surface	tinned	Housing main material	CuZn
Insulation resistance	10 ⁸ Ω	No. of poles	4
Plugging cycles	≥ 50	Pollution severity	3
Protection degree	IP 67	Rated current	4 A
Rated voltage	32 V	Rated voltage (text)	32 V
Shield connection	No	Threaded ring material	Diecast zinc
Type of connection	Insulation displacement connection		

Classifications

ETIM 3.0	EC002062	UNSPSC	30-21-18-10
eClass 5.1	27-26-07-01	eClass 6.2	27-26-07-02
eClass 7.1	27-44-01-02		

Approvals

Approvals	
ROHS	Conform