

**HDC enclosures**  
**HDC 16D SLU 2M25G****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

**General ordering data**

|            |                                                                                                                                    |
|------------|------------------------------------------------------------------------------------------------------------------------------------|
| Type       | HDC 16D SLU 2M25G                                                                                                                  |
| Order No.  | <a href="#">1787520000</a>                                                                                                         |
| Version    | HDC enclosures, Size: 3, Protection degree: IP65, Base enclosure, End-locking clamp, lower side, high, Size of cable entries: M 25 |
| GTIN (EAN) | 4032248204861                                                                                                                      |
| Qty.       | 1 pc(s).                                                                                                                           |

**HDC enclosures**  
**HDC 16D SLU 2M25G**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

|                            |         |                             |            |
|----------------------------|---------|-----------------------------|------------|
| Width                      | 71.7 mm | Width (inches)              | 2.823 inch |
| Height                     | 74 mm   | Height (inches)             | 2.913 inch |
| Mounting dimension - width | 70 mm   | Mounting dimension - height | 45 mm      |
| Net weight                 | 301 g   |                             |            |

**Temperatures**

|                   |                   |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

**Environmental Product Compliance**

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

**Dimensions**

|                      |              |                      |         |
|----------------------|--------------|----------------------|---------|
| Cable entry          | w. threading | Height of base B1    | 5 mm    |
| Height of housing B  | 74 mm        | Hole pitch length A2 | 70 mm   |
| Total length housing | 60 mm        | Width base C1        | 54.5 mm |
| Width housing C      | 43 mm        |                      |         |

**General data**

|                             |                             |                       |                   |
|-----------------------------|-----------------------------|-----------------------|-------------------|
| EMC housings                | No                          | Housing main material | diecast aluminium |
| Material of locking element | Stainless steel, rust-proof | Protection degree     | IP65              |
| Surface finish              | Powder coating              |                       |                   |

**Version**

|                              |                               |                                |                   |
|------------------------------|-------------------------------|--------------------------------|-------------------|
| Cable entry                  | w. threading                  | Clamp version                  | End-locking clamp |
| Design                       | high                          | Design of housing              | Base enclosure    |
| Design of locking system     | End-locking clamp, lower side | Internal thread                | M 25              |
| Number of cable entry on top | 0                             | Number of cable entry sideways | 2                 |
| Sealing                      | NBR                           | Size                           | 3                 |
| Size of cable entries        | M 25                          | Suitable for ModuPlug®         | Yes               |
| Top part/bottom part/lid     | lower part                    | Type                           | Base housing      |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000437    | ETIM 4.0   | EC000437    |
| ETIM 5.0   | EC000437    | ETIM 6.0   | EC000437    |
| UNSPSC     | 30-21-18-01 | eClass 5.1 | 27-14-34-19 |
| eClass 6.2 | 27-26-12-03 | eClass 7.1 | 27-44-02-02 |
| eClass 8.1 | 27-44-02-02 | eClass 9.0 | 27-44-02-02 |
| eClass 9.1 | 27-44-02-02 |            |             |

**Approvals**

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### HDC enclosures HDC 16D SLU 2M25G

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

|                         |                                                                         |
|-------------------------|-------------------------------------------------------------------------|
| Brochure/Catalogue      | <a href="#">CAT 3 HDC 17/18 EN</a><br><a href="#">FL FIELDWIRING EN</a> |
| Engineering Data        | <a href="#">EPLAN, WSCAD</a>                                            |
| Engineering Data        | <a href="#">STEP</a>                                                    |
| Technical Documentation | <a href="#">1787520000_HDC_16D_SLU_2M25G_STP_Blatt_1.pdf</a>            |

### HDC enclosures HDC 16D SLU 2M25G

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

