

SAISW-4/8S-M12 4P D-ZF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



M12 plug-in connector in IP 67 available with crew or
tension clamp connection

General ordering data

Type	SAISW-4/8S-M12 4P D-ZF
Order No.	1803930001
Version	Sockets prefabricated to customer spec., Plugs prefabricated to customer spec., M12, pin, 90°
GTIN (EAN)	4032248647958
Qty.	1 pc(s).

SAISW-4/8S-M12 4P D-ZF

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 64 g

Downloads

GOST Approval POCC
 DE.ME25.B01411.pdf

General Info

Contact surface	Gold-plated	Contact tube diameter	M12
Description of article	SAIS-ZF	Housing main material	PA
Plugging cycles	≥ 100	Protection degree	IP 67

Electrical properties

Insulation resistance $10^8 \Omega$ Rated voltage 250 V

Standards

Connector standard IEC 61076-2-101

Classifications

ETIM 3.0	EC002062	UNSPSC	30-21-18-01
eClass 5.1	27-26-07-01	eClass 6.2	27-26-07-02
eClass 7.1	27-44-01-02		

Approvals

Approvals



ROHS Conform