

SAIB-4/9**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

General ordering data

Type	SAIB-4/9
Order No.	1807230000
Version	Sockets prefabricated to customer spec., Plugs prefabricated to customer spec., M12, Female socket, straight
GTIN (EAN)	4032248278213
Qty.	1 pc(s).

SAIB-4/9

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 26 g

Technical data customisable plug-in connectors

Cable diameter	4...6 mm (PG7)/ 6...8 mm (PG9)	Cable diameter, max.	8 mm
Cable diameter, min.	6 mm	Cable gland	PG 9
Coding	A	Connection cross-section, max.	0.75 mm ²
Connection cross-section, min.	0.14 mm ²	Contact surface	CuSnZn
Housing main material	PA	Insulation resistance	10 ⁸ Ω
No. of poles	4	Plugging cycles	500
Pollution severity	3	Protection degree	IP 67
Rated current	4 A	Rated voltage	250 V
Rated voltage (text)	250 V (4-pole) / 125 V (5-pole)	Shield connection	No
Threaded ring material	Diecast zinc	Type of connection	Screw connection

Classifications

ETIM 3.0	EC002062	UNSPSC	30-21-18-10
eClass 5.1	27-26-07-01	eClass 6.2	27-26-07-02
eClass 7.1	27-44-01-02		

Approvals

Approvals



ROHS Conform