

SAIE-M8B-3-0.5U-FP-M8**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Type	SAIE-M8B-3-0.5U-FP-M8
Order No.	1856130000
Version	Built-in plugs, M8, Female socket, straight, M 8, No. of poles: 3, 0.5 m
GTIN (EAN)	4032248398997
Qty.	1 pc(s).

SAIE-M8B-3-0.5U-FP-M8

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 13 g

General data

Cable gland	M 8	Cable length	0.5 m
Conductor O.D.	-	Contact surface	Gold-plated
Contact tube diameter	M8	Core cross-section	0.25 mm ²
Housing main material	CuZn, nickel-plated	Material	PVC
No. of poles	3	Protection degree	IP 67
Rated current	4 A	Rated voltage	60 V
Rated voltage (text)	60 V (3-pole) / 30 V (4-pole)	Strand cable length	0.5 m
Temperature range of housing	-30...+90 °C	Type of connection	Socket

Classifications

ETIM 3.0	EC002061	UNSPSC	30-21-18-10
eClass 5.1	27-26-07-01	eClass 6.2	27-26-07-02
eClass 7.1	27-44-01-02		

Approvals

Approvals



ROHS Conform