

SAIL-VSBD-M12W-3.0U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Weidmüller can supply valve plugs as connecting lines with M12 plugs and one end without connector. The status of the valve plug is shown by an LED. Every valve plug is fitted with a protective circuit. The Weidmüller range includes valve plugs of type A, B and C to DIN and industry standards. In the plugged condition they achieve IP 67 class of protection. The outlet direction is also a decisive factor: Weidmüller can also supply 0° versions, i.e. the cable outlet direction is located at the PE contact.

General ordering data

Type	SAIL-VSBD-M12W-3.0U
Order No.	1857710300
Version	Valve plug, 90° plug - valve plug, BD
GTIN (EAN)	4032248404032
Qty.	1 pc(s).

SAIL-VSBD-M12W-3.0U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	192 g
------------	-------

Technical specifications for cable

Core cross-section	0.5 mm ²	shielded	No
Sheath material	PUR	Sheathing colour	Black
Cable length	3 m	Halogen	No

General technical data

Version	90° plug - valve plug	Contact tube diameter	Miscellaneous
Coding	DIN design B (10 mm), M12 = A	Protection degree	IP 67 (when screwed in)
Contact surface	tinned	LED	Yes
Rated voltage	24 V	Rated current	4 A
Temperature range of housing	-25...+80 °C		

Classifications

ETIM 3.0	EC001855	UNSPSC	30-21-18-10
eClass 5.1	27-26-07-01	eClass 6.2	27-27-92-18
eClass 7.1	27-06-91-90		

Approvals

Approvals	
ROHS	Conform