SAIL-VSCD-M12W-3.0U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



This valve plug has a transparent housing with an integral seal. The connection cross-section corresponds to 0.5 mm² and can therefore be connected directly to our SAI IDC distributor. The operating status of the valve plug is indicated by an LED. All the valve plugs have a protective circuit. The Weidmüller range of products comprises valve plugs type A, B and C to DIN and industry standards. In the plugged condition they achieve IP 67 class of protection.

General ordering data

Type	SAIL-VSCD-M12W-3.0U
Order No.	1857730300
Version	Valve plug, 90° plug - valve plug, CD
GTIN (EAN)	4032248404162
Qty.	1 pc(s).

SAIL-VSCD-M12W-3.0U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	177 g

Technical specifications for cable

Core cross-section	0.5 mm²	shielded	No
Sheath material	PUR	Sheathing colour	Black
Cable length	3 m	Halogen	No

General technical data

Version	90° plug - valve plug	Contact tube diameter	Miscellaneous
Coding	DIN design C (8 mm), M12 = A	Protection degree	IP 67 (when screwed in)
Contact surface	tinned	LED	Yes
Rated voltage	24 V	Rated current	4 A
Temperature range of housing	-25...+80 °C		

Classifications

ETIM 3.0	EC001855	UNSPSC	30-21-18-10
eClass 5.1	27-26-07-01	eClass 6.2	27-27-92-18
eClass 7.1	27-06-91-90		

Approvals

Approvals
ROHS Conform