

SAIE-M12B-8-0.5U-PG9**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Type	SAIE-M12B-8-0.5U-PG9
Order No.	1861270000
Version	Built-in plugs, M12, Female socket, straight, PG 9, No. of poles: 8, 0.5 m
GTIN (EAN)	4032248419340
Qty.	1 pc(s).

SAIE-M12B-8-0.5U-PG9

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	33 g
------------	------

General data

Cable gland	PG 9	Cable length	0.5 m
Conductor O.D.	-	Contact surface	Gold-plated
Contact tube diameter	M12	Core cross-section	0.25 mm ²
Housing main material	CuZn, nickel-plated	Material	PVC
No. of poles	8	Protection degree	IP 67
Rated voltage	30 V	Rated voltage (text)	250 V (4-pole) / 125 V (5-pole) / 60 V (8-pole)
Strand cable length	0.5 m	Temperature range of housing	-30...+90 °C
Type of connection	Socket		

Classifications

ETIM 3.0	EC002061	UNSPSC	30-21-18-10
eClass 5.1	27-26-07-01	eClass 6.2	27-26-07-02
eClass 7.1	27-44-01-02		

Approvals

Approvals



ROHS	Conform
------	---------