SAIE-M5S-3-0.2U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Type	SAIE-M5S-3-0.2U
Order No.	1873050000
Version	Built-in plugs, M5, pin, straight, M 5, No. of poles: 3, 0.2 m
GTIN (EAN)	4032248478415
Qty.	1 pc(s).

SAIE-M5S-3-0.2U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	4 g

General data

Cable gland	M 5	Cable length	0.2 m
Conductor O.D.	-	Contact surface	Gold-plated
Contact tube diameter	M5	Core cross-section	0.14 mm²
Housing main material	CuZn, nickel-plated	Material	PVC
No. of poles	3	Protection degree	IP 67
Rated current	1 A	Rated voltage	60 V
Rated voltage (text)	60 V	Strand cable length	0.2 m
Temperature range of housing	-25...+80 °C	Type of connection	Pin

Classifications

ETIM 3.0	EC002061	UNSPSC	30-21-18-10
eClass 5.1	27-26-07-01	eClass 6.2	27-26-07-02
eClass 7.1	27-44-01-02		

Approvals

Approvals	ME25
ROHS	Conform