

Screwty M12 KO o. SD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The Screwty® attachment is suitable for M12 round plug-in connectors, with an outside dimension of the knurled nut of 14.5 ± 0.3 mm. The tightening torque is 0.8-1.2 Nm.

General ordering data

Type	Screwty M12 KO o. SD
Order No.	1900100000
Version	Tools, Cable gland tool for moulded M12 lines
GTIN (EAN)	4032248409952
Qty.	1 pc(s).

Screwty M12 KO o. SD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten**Dimensions and weights**

Net weight	17 g
------------	------

Classifications

ETIM 3.0	EC000174	eClass 6.2	21-04-01-90
eClass 7.1	21-04-01-90		

Approvals

Approvals	
ROHS	Conform