

**Screwty M12f KO o. SD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The Screwty® attachment is suitable for customisable M12 round plug-in connectors, with an outside dimension of the knurled nut of  $19.8 \pm 0.3$  mm. The tightening torque is 0.8-1.2 Nm.

**General ordering data**

|            |  |
|------------|--|
| Type       | Screwty M12f KO o. SD                      |
| Order No.  | <a href="#">1900120000</a>                 |
| Version    | Tools, Cable gland tool for M12 connectors |
| GTIN (EAN) | 4032248409976                              |
| Qty.       | 1 pc(s).                                   |

**Datenblatt****Screwty M12f KO o. SD**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technische Daten****Dimensions and weights**

|            |      |
|------------|------|
| Net weight | 18 g |
|------------|------|

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000174    | eClass 6.2 | 21-04-01-90 |
| eClass 7.1 | 21-04-01-90 |            |             |

**Approvals**

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |