



MODEL	VOLTAGE		NO LOAD		AT MAXIMUM EFFICIENCY				STARTING		max. OUTPUT POWER W	POLES	CAPACITOR	BRUSHES
	Operating Range	Nominal	Speed	Current	Speed	Current	Torque	Output Power	Current	Torque				
	VDC	VDC	rpm	A	rpm	A	mNm	W	A	mNm				
FF-K10WA-5Z215	2,0-4,0	3,0	21.000	0,06	13.268	0,10	0,10	0,14	0,18	0,27	0,15	3	none	metal



Irrtum und Druckfehler vorbehalten / Errors and Omissions excepted